## TS-9-B8HD HEAVY DUTY LOAD MODULE SYSTEM

Technical specification:

Type TS-9-B8HD

Capacity 9,120 lbs.

Composition - 4 aluminium supporting plates with air caster element B8HD

- 5 hoses with quick connect couplings

- 1 air regulator manifold

- 1 User Manual

<u>Air casters</u> B8HD, with a max. capacity of 2,280 lbs at 60 psi.

The air consumption is approx. 12 cfm each, depending on the

adjustment, the load and the quality of the floor.

<u>Dimensions</u> The air caster element consists of an aluminium plate and an air caster

B8HD. Dimensions 8 x 8 x 1 3/16 in with integrated air through let.

<u>Air regulation</u> The air regulation is composed of a steel box on castors with two

handles and dimensions L x W x H = ca. 20 x 10 x 10 in.

The important parts of this unit are:

1. safety connections for the air supply to the air regulation unit

ball valve as main valve in the main air supply
pressure gauge to indicate supply pressure
regulator to adjust the pressure in each air caster

pressure gauge to indicate pressure in each air caster
safety couplings for the air supply to each air caster

the air regulation unit is finished in safety yellow (RAL 1018).

Hoses 1 main air supply hose 1/2" of 33ft with safety quick connect couplings.

other lengths on request for an additional price 2 hoses 3/8" of 10ft with safety couplings. 2 hoses 3/8" of 16ft with safety couplings.

The lift The lift is approx. ¼" in depending on the adjustment, the load and the

floor. By placing the object on supports of 1 1/4 in height, it can at any time

be picked up and transported with the air casters.

Operation The operation of the air caster is being done with the on / off ball valve

and the pressure regulators on the regulation unit. For a more extensive

instruction to operate please refer to the manual.

Manual We can supply you with a manual in one of the following languages:

English, German, French and Dutch.

Floor The floor is an important part of the air caster transport system. In

order to create sufficient air film and a minimal air consumption the floor has to be of a sufficient quality. See for more information our brochure:

" Air cushion transport and the floor" .

technical changes reserved